

Körüklü vantuz (oval)

FGAO 18x14 SI-HD-65 N016

Art.-Nr.: 10.01.06.02458




Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI-HD
Malzeme sertliği [Shore A]	65,0 Shore A
Yükseklik H	13,50 mm

FGAO 18x14 SI-HD-65 N016

Tasarım verileri



Attribute	Value
Uzunluk L1	18,20 mm
Genişlik B1	13,70 mm
Yükseklik H	13,50 mm
İç çap d	4,50 mm
Yay stroku Z	5,0 mm
Vantuz genişliği Bs	12,50 mm
Ls	16,90 mm
Lmaks.(S)	18,50 mm
Bmax(S)	14,00 mm
Uzunluk L2	9,50 mm
Genişlik B2	5,00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri FGAO 18x14 SI-HD-65 N016



WWW.SCHMALZ.COM/10.01.06.02458

Körüklü vantuz (oval)

FGAO 18x14 SI-HD-65 N016



Art.-Nr.: 10.01.06.02458



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI-HD
Malzeme sertliği [Shore A]	65,0 Shore A
İş parçası yarıçapı dak (dışbükey)	6,0 mm
Emme kuvveti (-600mbar)	2,10 N
Ağırlık	1,20 g
Boyutlar (LxW)	18 x 14
Körük Sayısı	1,5
Ürün ailesi	FGAO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02458



WWW.SCHMALZ.COM/10.01.06.02458