




SAB 125 HT1-60 G3/8-IG

Çeşitli çaplarda mevcut olan vantuz SAB HT1, elastomer parçaya vulkanize edilmiş bağlantı nipeli ile birlikte teslim edilir.



Tasarım verileri SAB 125 HT1-60 G3/8-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Boyut	125.00
Körük Sayısı	1.5
Bağlantı	G3/8-IG
Meme ucu malzemesi	Alüminyum

Tasarım verileri

Attribute	Value
Yükseklik H	67.80 mm
Dış çap D1	94.0 mm
Nominal çap dn	9.00 mm
Dış G1	G3/8"-F
Dış uzunluğu LG1	15.0 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	32.0 mm
Çap Ds	126.0 mm
Çap Dmax(S)	135.0 mm

Art.-Nr.: 10.01.06.02729

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Hortum çapı (tavsiye edilen) d	9.0 mm
İş parçası yarıçapı dak (dışbükey)	140.0 mm
Çekme kuvveti	558.00 N
Emme kuvveti (-600mbar)	250.00 N
Ağırlık	170.2 g
Yanal kuvvet	352.0 N
Yanal kuvvet yağlı yüzey	335.0 N
Cilt	220.000 cm ³
Boyut	125.00
Körük Sayısı	1.5
Ürün ailesi	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02729

WWW.SCHMALZ.COM/10.01.06.02729