


Технические данные

Attribute	Value
Материал присоски	Высокотемпературный материал HT1
Твердость материала [Shore A]	60,0 Shore A
размер	62,00
Количество складок	2,5

FG 62 HT1-60 N018



Конструктивные данные

Attribute	Value
Высота H2	13,00 mm
Высота H	54,00 mm
Наружный диаметр D1	62,0 mm
Диаметр головки Dk	18,0 mm
d2	29,5 mm
Внутренний диаметр d	8,00 mm
Ход пружины Z	29,0 mm
Диаметр Ds	62,2 mm
Диаметр Dmax(S)	65,0 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Конструктивные данные FG 62 HT1-60 N018

Art.-Nr.: 10.01.06.02475



Технические данные

Attribute	Value
Семейство ниппелей	N 018
Материал присоски	Высокотемпературный материал HT1
Твердость материала [Shore A]	60,0 Shore A
Радиус заготовки мин. (выпуклый)	42,0 mm
Сила отрыва	137,00 N
Всасывающая сила (-600 мбар)	41,01 N
Вес	39,2 g
Объем	61,122 cm ³
размер	62,00
Количество складок	2,5
Семейство продуктов	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02475

