


SAB 50 HT1-60 G1/4-IG

Çeşitli çaplarda mevcut olan vantuz SAB HT1, elastomer parçaya vulkanize edilmiş bağlantı nipeli ile birlikte teslim edilir.



Tasarım verileri SAB 50 HT1-60 G1/4-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Boyut	50.00
Körük Sayısı	1.5
Bağlantı	G1/4-IG
Meme ucu malzemesi	Nikel kaplama

Tasarım verileri

Attribute	Value
Yükseklik H	42.00 mm
Dış çap D1	39.5 mm
Nominal çap dn	6.00 mm
Dış G1	G1/4"-F
Dış uzunluğu LG1	20.0 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	11.6 mm
Çap Ds	50.1 mm
Çap Dmax(S)	56.0 mm

Art.-Nr.: 10.01.06.02760



Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Hortum çapı (tavsiye edilen) d	4.0 mm
İş parçası yarıçapı dak (dışbükey)	50.0 mm
Çekme kuvveti	87.00 N
Emme kuvveti (-600mbar)	53.00 N
Ağırlık	45.2 g
Yanal kuvvet	55.0 N
Yanal kuvvet yağlı yüzey	52.0 N
Cilt	16.100 cm ³
Boyut	50.00
Körük Sayısı	1.5
Ürün ailesi	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02760

