


FGA 53 NK-45 N018 DR

Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45.0 Shore A
Boyut	53.00
Körük Sayısı	1.5



Tasarım verileri FGA 53 NK-45 N018 DR

Tasarım verileri

Attribute	Value
Yükseklik H2	12.30 mm
Yükseklik H	36.00 mm
Dış çap D1	58.6 mm
Kafa çapı Dk	18.0 mm
d2	33.0 mm
İç çap d	8.00 mm
Yay stroku Z	15.0 mm
Çap Ds	39.0 mm
Yükseklik H3	19.00 mm
Çap Dmax(S)	60.0 mm

Art.-Nr.: 10.01.06.02929

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 018
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45.0 Shore A
İş parçası yarıçapı dak (dışbükey)	75.0 mm
Çekme kuvveti	95.00 N
Emme kuvveti (-600mbar)	51.30 N
Ağırlık	18.3 g
Cilt	28.400 cm ³
Boyut	53.00
Körük Sayısı	1.5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02929

WWW.SCHMALZ.COM/10.01.06.02929