



FG 4 HT1-60 N017


Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Boyut	4.00
Körük Sayısı	2.5

Tasarım verileri

Attribute	Value
Yükseklik H2	3.90 mm
Yükseklik H	14.00 mm
Dış çap D1	5.1 mm
Kafa çapı Dk	7.0 mm
d2	2.4 mm
İç çap d	3.50 mm
Yay stroku Z	1.5 mm
Çap Ds	3.8 mm
Yükseklik H3	7.00 mm
Çap Dmax(S)	5.5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FG 4 HT1-60 N017

Art.-Nr.: 10.01.06.02930



Teknik veriler

Attribute	Value
Meme ucu ailesi	N 017
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
İş parçası yarıçapı dak (dışbükey)	4.0 mm
Çekme kuvveti	0.60 N
Emme kuvveti (-600mbar)	0.27 N
Ağırlık	0.4 g
Cilt	0.124 cm ³
Boyut	4.00
Körük Sayısı	2.5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02930



WWW.SCHMALZ.COM/10.01.06.02930