


FSGPL 120 NBR-55 G1/2-IG

Çeşitli çaplarda mevcut olan FSGPL vantuz, elastomer parçaya vulkanize edilmiş destek plakası ile birlikte teslim edilir.



Tasarım verileri FSGPL 120 NBR-55 G1/2-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	120.00
Körük Sayısı	1.5
Vakum bağlantısı	G1/2"-F
Meme ucu malzemesi	Çelik

Tasarım verileri

Attribute	Value
Yükseklik H	51.00 mm
Dış çap D1	127.8 mm
d2	79.3 mm
Dış G1	G1/2"-F
Dış uzunluğu LG1	8.0 mm
Delik boyutu d3	69.4 mm
Yay stroku Z	35.7 mm
Çap Ds	118.2 mm
Yükseklik H4	8.00 mm
Çap Dmax(S)	135.0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.02933

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	12.0 mm
İş parçası yarıçapı dak (dışbükey)	150.0 mm
Çekme kuvveti	400.00 N
Emme kuvveti (-600mbar)	280.00 N
Ağırlık	351.0 g
Cilt	295.203 cm ³
Boyut	120.00
Körük Sayısı	1.5
Ürün ailesi	FSGPL

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02933

WWW.SCHMALZ.COM/10.01.06.02933