

Bellows suction cup HT1 (round)

SAB 100 HT1-60 G1/4-IG



Art.-Nr.: 10.01.06.02961




Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	100.00
Number of folds	1.5
Connection	G1/4-IG
Nipple material	Nickel plated

SAB 100 HT1-60 G1/4-IG

Suction cup SAB HT1, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.



Design data

Height H	61.80 mm
Outside diameter D1	77.0 mm
Nominal diameter dn	6.00 mm
Thread G1	G1/4"-F
Thread length LG1	20.0 mm
Key width SW1	22.0 mm
Spring stroke Z	25.8 mm
Diameter Ds	100.8 mm
Diameter Dmax(S)	110.0 mm

Design data SAB 100 HT1-60 G1/4-IG



WWW.SCHMALZ.COM/10.01.06.02961

Art.-Nr.: 10.01.06.02961

**Technical data**

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	90.0 mm
Pull-off force	357.00 N
Suction force (-600mbar)	190.00 N
Weight	101.90 g
Lateral force	220.0 N
Lateral force oily surface	214.0 N
Volume	115.000 cm ³
Size	100.00
Number of folds	1.5
Product family	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

