


Körüklü vantuz (yuvarlak)

FGA 78 NK-45 N019 DR




Art.-Nr.: 10.01.06.02977



Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45.0 Shore A
Boyut	78.00
Körük Sayısı	1.5

FGA 78 NK-45 N019 DR



Tasarım verileri

Attribute	Value
Yükseklik H2	19.70 mm
Yükseklik H	48.50 mm
Dış çap D1	83.0 mm
Kafa çapı Dk	24.7 mm
d2	54.0 mm
İç çap d	11.80 mm
Yay stroku Z	16.0 mm
Çap Ds	62.0 mm
Yükseklik H3	31.40 mm
Çap Dmax(S)	86.0 mm

Tasarım verileri FGA 78 NK-45 N019 DR



WWW.SCHMALZ.COM/10.01.06.02977

Art.-Nr.: 10.01.06.02977



Teknik veriler

Attribute	Value
Meme ucu ailesi	N 019
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45.0 Shore A
İş parçası yarıçapı dak (dışbükey)	70.0 mm
Çekme kuvveti	218.00 N
Emme kuvveti (-600mbar)	137.40 N
Ağırlık	48.0 g
Cilt	79.418 cm ³
Boyut	78.00
Körük Sayısı	1.5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02977



WWW.SCHMALZ.COM/10.01.06.02977