



Art.-Nr.: 10.01.06.02978



FSGPL 100 NBR-55 G1/2-IG DR

Sızdırmazlık halkalı körüklü vantuz, çeşitli çaplarda mevcuttur, sızdırmazlık halkası yapıştırılmış olarak teslim edilir.



Tasarım verileri FSGPL 100 NBR-55 G1/2-IG DR

## Teknik veriler

| Attribute                  | Value             |
|----------------------------|-------------------|
| Vantuz malzemesi           | Nitril kauçuk NBR |
| Malzeme sertliği [Shore A] | 55.0 Shore A      |
| Boyut                      | 100.00            |
| Körük Sayısı               | 1.5               |
| Meme ucu malzemesi         | Çelik             |

## Tasarım verileri

| Attribute        | Value    |
|------------------|----------|
| Yükseklik H      | 43.30 mm |
| Dış çap D1       | 101.0 mm |
| d2               | 57.2 mm  |
| Dış G1           | G1/2"-F  |
| Dış uzunluğu LG1 | 8.0 mm   |
| Delik boyutu d3  | 44.0 mm  |
| Yay stroku Z     | 29.1 mm  |
| Çap Ds           | 67.0 mm  |
| Yükseklik H4     | 8.00 mm  |
| Çap Dmax(S)      | 106.5 mm |

Art.-Nr.: 10.01.06.02978



## Teknik veriler

| Attribute                          | Value                   |
|------------------------------------|-------------------------|
| Vantuz malzemesi                   | Nitril kauçuk NBR       |
| Malzeme sertliği [Shore A]         | 55.0 Shore A            |
| Hortum çapı (tavsiye edilen) d     | 12.0 mm                 |
| İş parçası yarıçapı dak (dışbükey) | 100.0 mm                |
| Ağırlık                            | 154.0 g                 |
| Cilt                               | 150.000 cm <sup>3</sup> |
| Boyut                              | 100.00                  |
| Körük Sayısı                       | 1.5                     |
| Ürün ailesi                        | FSGPL                   |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



## Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.06.02978](http://www.schmalz.com/10.01.06.02978)



[WWW.SCHMALZ.COM/10.01.06.02978](http://WWW.SCHMALZ.COM/10.01.06.02978)