


Art.-Nr.: 10.01.06.02760



SAB 50 HT1-60 G1/4-IG


Suction cup SAB HT1, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	50.00
Number of folds	1.5
Connection	G1/4-IG
Nipple material	Nickel plated

Design data

Attribute	Value
Height H	42.00 mm
Outside diameter D1	39.5 mm
Nominal diameter dn	6.00 mm
Thread G1	G1/4"-F
Thread length LG1	20.0 mm
Key width SW1	22.0 mm
Spring stroke Z	11.6 mm
Diameter Ds	50.1 mm
Diameter Dmax(S)	56.0 mm



Design data SAB 50 HT1-60 G1/4-IG



Art.-Nr.: 10.01.06.02760

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	50.0 mm
Pull-off force	87.00 N
Suction force (-600mbar)	53.00 N
Weight	45.2 g
Lateral force	55.0 N
Lateral force oily surface	52.0 N
Volume	16.100 cm ³
Size	50.00
Number of folds	1.5
Product family	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02760

