


Bellows suction cups (round)

FSGPL 120 NBR-55 G1/2-IG DR



Art.-Nr.: 10.01.06.02993




Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Size	120.00
Number of folds	1.5
Nipple material	Steel

FSGPL 120 NBR-55 G1/2-IG DR

Bellows suction cup with sealing ring, available in various diameters, delivered with sealing ring glued on.



Design data

Attribute	Value
Height H	51.00 mm
Outside diameter D1	127.8 mm
d2	79.3 mm
Thread G1	G1/2"-F
Thread length LG1	8.0 mm
Hole size d3	69.4 mm
Spring stroke Z	35.7 mm
Diameter Ds	96.0 mm
Height H4	8.00 mm
Diameter Dmax(S)	135.0 mm

Design data FSGPL 120 NBR-55 G1/2-IG DR



WWW.SCHMALZ.COM/10.01.06.02993

Art.-Nr.: 10.01.06.02993

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	12.0 mm
Workpiece radius min. (convex)	150.0 mm
Weight	354.0 g
Volume	290.675 cm ³
Size	120.00
Number of folds	1.5
Product family	FSGPL

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02993

