




FG 4 SI-55 N017

## Технические данные

| Attribute                     | Value             |
|-------------------------------|-------------------|
| Материал присоски             | Силикон SI        |
| Твердость материала [Shore A] | 55,0 Shore A      |
| размер                        | 4,00              |
| Количество складок            | 2,5               |
| Характеристики материала      | Совместимый с FDA |



Конструктивные данные FG 4 SI-55 N017

## Конструктивные данные

| Attribute             | Value    |
|-----------------------|----------|
| Высота H2             | 3,90 mm  |
| Высота H              | 14,00 mm |
| Наружный диаметр D1   | 5,1 mm   |
| Диаметр головки Dk    | 7,0 mm   |
| Внутренний диаметр d1 | 3,9 mm   |
| d2                    | 2,4 mm   |
| Внутренний диаметр d  | 3,50 mm  |
| Ход пружины Z         | 1,5 mm   |
| Диаметр Ds            | 3,8 mm   |
| Высота H3             | 7,00 mm  |

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Art.-Nr.: 10.01.06.02963



## Технические данные

| Attribute                        | Value                 |
|----------------------------------|-----------------------|
| Семейство ниппелей               | N 017                 |
| Материал присоски                | Силикон SI            |
| Твердость материала [Shore A]    | 55,0 Shore A          |
| Радиус заготовки мин. (выпуклый) | 4,0 mm                |
| Сила отрыва                      | 0,60 N                |
| Всасывающая сила (-600 мбар)     | 0,27 N                |
| Вес                              | 0,4 g                 |
| Объем                            | 0,124 cm <sup>3</sup> |
| размер                           | 4,00                  |
| Количество складок               | 2,5                   |
| Семейство продуктов              | FG                    |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



## Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.06.02963](http://www.schmalz.com/10.01.06.02963)

