

Сильфонная присоска (круглая)
FGA 78 NK-45 N019 DR




Art.-Nr.: 10.01.06.02977



FGA 78 NK-45 N019 DR

Технические данные

Attribute	Value
Материал присоски	Натуральная резина НК
Твердость материала [Shore A]	45,0 Shore A
размер	78,00
Количество складок	1,5



Конструктивные данные FGA 78 NK-45 N019 DR

Конструктивные данные

Attribute	Value
Высота H2	19,70 mm
Высота H	48,50 mm
Наружный диаметр D1	83,0 mm
Диаметр головки Dk	24,7 mm
d2	54,0 mm
Внутренний диаметр d	11,80 mm
Ход пружины Z	16,0 mm
Диаметр Ds	62,0 mm
Высота H3	31,40 mm
Диаметр Dmax(S)	86,0 mm



WWW.SCHMALZ.COM/10.01.06.02977

Сильфонная присоска (круглая)
FGA 78 NK-45 N019 DR



Art.-Nr.: 10.01.06.02977



Технические данные

Attribute	Value
Семейство ниппелей	N 019
Материал присоски	Натуральная резина НК
Твердость материала [Shore A]	45,0 Shore A
Радиус заготовки мин. (выпуклый)	70,0 mm
Сила отрыва	218,00 N
Всасывающая сила (-600 мбар)	137,40 N
Вес	48,0 g
Объем	79,418 cm ³
размер	78,00
Количество складок	1,5
Семейство продуктов	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02977



WWW.SCHMALZ.COM/10.01.06.02977