


Körüklü vantuz HT1 (yuvarlak)

SAB 60 HT1-60 G3/8-AG



Art.-Nr.: 10.01.06.03060




Teknik veriler

Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	60,00
Körük Sayısı	1,5
Bağlantı	G3/8-AG
Meme ucu malzemesi	Alüminyum

SAB 60 HT1-60 G3/8-AG

Çeşitli çaplarda mevcut olan vantuz SAB HT1, elastomer parçaya vulkanize edilmiş bağlantı nipelini ile birlikte teslim edilir.



Tasarım verileri

Yükseklik H	41,30 mm
Dış çap D1	48,0 mm
Nominal çap dn	6,00 mm
Dış G1	G3/8"-M
Dış uzunluğu LG1	10,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	14,5 mm
Çap Ds	61,1 mm
Çap Dmax(S)	67,0 mm

Tasarım verileri SAB 60 HT1-60 G3/8-AG



WWW.SCHMALZ.COM/10.01.06.03060

Art.-Nr.: 10.01.06.03060



Teknik veriler

Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Hortum çapı (tavsiye edilen) d	6,0 mm
İş parçası yarıçapı dak (dışbükey)	65,0 mm
Çekme kuvveti	130,00 N
Emme kuvveti (-600mbar)	82,00 N
Ağırlık	50,90 g
Yanal kuvvet	82,0 N
Yanal kuvvet yağlı yüzey	77,0 N
Cilt	28,800 cm ³
Boyut	60,00
Körük Sayısı	1,5
Ürün ailesi	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

