

Bellows suction cup HT1 (round)

SAB 60 HT1-60 G3/8-AG



Art.-Nr.: 10.01.06.03060




Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	60.00
Number of folds	1.5
Connection	G3/8-AG
Nipple material	Aluminum

SAB 60 HT1-60 G3/8-AG

Suction cup SAB HT1, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.



Design data

Height H	41.30 mm
Outside diameter D1	48.0 mm
Nominal diameter dn	6.00 mm
Thread G1	G3/8"-M
Thread length LG1	10.0 mm
Key width SW1	22.0 mm
Spring stroke Z	14.5 mm
Diameter Ds	61.1 mm
Diameter Dmax(S)	67.0 mm

Design data SAB 60 HT1-60 G3/8-AG



WWW.SCHMALZ.COM/10.01.06.03060

1

Art.-Nr.: 10.01.06.03060

**Technical data**

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	65.0 mm
Pull-off force	130.00 N
Suction force (-600mbar)	82.00 N
Weight	50.90 g
Lateral force	82.0 N
Lateral force oily surface	77.0 N
Volume	28.800 cm ³
Size	60.00
Number of folds	1.5
Product family	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

