

Bellows suction cup HT1 (round)

SAB 30 HT1-60 G1/4-AG



Art.-Nr.: 10.01.06.03048



SAB 30 HT1-60 G1/4-AG


Suction cup SAB HT1, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	30.00
Number of folds	1.5
Connection	G1/4-AG
Nipple material	Aluminum

Design data

Attribute	Value
Height H	28.00 mm
Outside diameter D1	32.0 mm
Nominal diameter dn	4.00 mm
Thread G1	G1/4"-M
Thread length LG1	10.0 mm
Key width SW1	17.0 mm
Spring stroke Z	9.0 mm
Diameter Ds	30.6 mm
Diameter Dmax(S)	34.0 mm



Design data SAB 30 HT1-60 G1/4-AG



WWW.SCHMALZ.COM/10.01.06.03048

Art.-Nr.: 10.01.06.03048

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	40.0 mm
Pull-off force	33.00 N
Suction force (-600mbar)	22.00 N
Weight	19.3 g
Lateral force	30.0 N
Lateral force oily surface	13.0 N
Volume	5.600 cm ³
Size	30.00
Number of folds	1.5
Product family	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03048

