

Bellows suction cup (round)

FG 4 NBR-CO-55 N017

Art.-Nr.: 10.01.06.03067



FG 4 NBR-CO-55 N017

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55.0 Shore A
Size	4.00
Number of folds	2.5

Design data

Attribute	Value
Height H2	3.90 mm
Height H	14.00 mm
Outside diameter D1	5.1 mm
Head diameter Dk	7.0 mm
d2	2.4 mm
Internal diameter d	3.50 mm
Spring stroke Z	1.5 mm
Diameter Ds	3.8 mm
Height H3	7.00 mm
Diameter Dmax(S)	5.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FG 4 NBR-CO-55 N017



WWW.SCHMALZ.COM/10.01.06.03067

Art.-Nr.: 10.01.06.03067

**Technical data**

Attribute	Value
Nipple family	N 017
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	4.0 mm
Pull-off force	0.60 N
Suction force (-600mbar)	0.27 N
Weight	0.4 g
Volume	0.124 cm ³
Size	4.00
Number of folds	2.5
Product family	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03067

