



Art.-Nr.: 10.01.06.03146



FSGPL 200 HT1-60 G1/2-IG

Suction cup FSGPL, available in various diameters, is delivered with support plate vulcanized to elastomer part.



Design data FSGPL 200 HT1-60 G1/2-IG

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	200.00
Number of folds	1.5
Vacuum connection	G1/2"-F
Nipple material	Steel
Material property	non-marking

Design data

Attribute	Value
Height H	54.00 mm
Outside diameter D1	202.0 mm
d2	137.0 mm
Thread G1	G1/2"-F
Thread length LG1	8.0 mm
Hole size d3	119.4 mm
Spring stroke Z	37.2 mm
Diameter Ds	191.0 mm
Height H4	8.00 mm
Diameter Dmax(S)	208.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Art.-Nr.: 10.01.06.03146

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	12.0 mm
Workpiece radius min. (convex)	350.0 mm
Pull-off force	950.00 N
Suction force (-600mbar)	850.00 N
Weight	1,014.5 g
Volume	876.516 cm ³
Size	200.00
Number of folds	1.5
Product family	FSGPL

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03146

