




FSGPL 100 HT1-60 G1/2-IG

Çeşitli çaplarda mevcut olan FSGPL vantuz, elastomer parçaya vulkanize edilmiş destek plakası ile birlikte teslim edilir.



Tasarım verileri FSGPL 100 HT1-60 G1/2-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Boyut	100.00
Körük Sayısı	1.5
Vakum bağlantısı	G1/2"-F
Meme ucu malzemesi	Çelik
Malzeme özelliği	iz bırakmayan

Tasarım verileri

Attribute	Value
Yükseklik H	43.30 mm
Dış çap D1	101.0 mm
d2	57.2 mm
Dış G1	G1/2"-F
Dış uzunluğu LG1	8.0 mm
Delik boyutu d3	44.0 mm
Yay stroku Z	29.1 mm
Çap Ds	96.1 mm
Yükseklik H4	8.00 mm
Çap Dmax(S)	106.5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.03150

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Hortum çapı (tavsiye edilen) d	12.0 mm
İş parçası yarıçapı dak (dışbükey)	100.0 mm
Emme kuvveti (-600mbar)	150.00 N
Ağırlık	145.0 g
Cilt	150.000 cm ³
Boyut	100.00
Körük Sayısı	1.5
Ürün ailesi	FSGPL

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03150

WWW.SCHMALZ.COM/10.01.06.03150