




Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65.0 Shore A
Boyut	80.00
Sıcaklık direnci	200.0 °C
Körük Sayısı	1.5
Bağlantı	G3/8-IG
Meme ucu malzemesi	Alüminyum

SAB 80 HT2-65 G3/8-IG

Çeşitli çaplarda mevcut olan vantuz SAB HT2, elastomer parçaya vulkanize edilmiş bağlantı nipeli ile birlikte teslim edilir.



Tasarım verileri

Attribute	Value
Yükseklik H	49.80 mm
Dış çap D1	65.0 mm
Nominal çap dn	6.00 mm
Dış G1	G3/8"-F
Dış uzunluğu LG1	15.0 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	22.0 mm
Çap Ds	81.2 mm
Çap Dmax(S)	88.0 mm

Tasarım verileri SAB 80 HT2-65 G3/8-IG

Art.-Nr.: 10.01.06.03318

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65.0 Shore A
Hortum çapı (tavsiye edilen) d	6.0 mm
İş parçası yarıçapı dak (dışbükey)	40.0 mm
Çekme kuvveti	221.00 N
Emme kuvveti (-600mbar)	135.00 N
Ağırlık	85.5 g
Yanal kuvvet	217.0 N
Cilt	67.600 cm ³
Boyut	80.00
Körük Sayısı	1.5
Bağlantı	G3/8"-F
Ürün ailesi	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03318

WWW.SCHMALZ.COM/10.01.06.03318