




SAB 80 HT2-65 G1/4-IG

Çeşitli çaplarda mevcut olan vantuz SAB HT2, elastomer parçaya vulkanize edilmiş bağlantı nipelini ile birlikte teslim edilir.



Tasarım verileri SAB 80 HT2-65 G1/4-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65,0 Shore A
Boyut	80,00
Sıcaklık direnci	200,0 °C
Körük Sayısı	1,5
Bağlantı	G1/4-IG
Meme ucu malzemesi	Alüminyum

Tasarım verileri

Attribute	Value
Yükseklik H	54,80 mm
Dış çap D1	65,0 mm
Nominal çap dn	6,00 mm
Dış G1	G1/4"-F
Dış uzunluğu LG1	15,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	22,0 mm
Çap Ds	81,2 mm
Çap Dmax(S)	88,0 mm

Art.-Nr.: 10.01.06.03356

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65,0 Shore A
Hortum çapı (tavsiye edilen) d	6,0 mm
İş parçası yarıçapı dak (dışbükey)	40,0 mm
Çekme kuvveti	238,00 N
Emme kuvveti (-600mbar)	135,00 N
Ağırlık	99,10 g
Yanal kuvvet	217,0 N
Cilt	67,600 cm ³
Boyut	80,00
Körük Sayısı	1,5
Bağlantı	G1/4" -F
Ürün ailesi	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03356

WWW.SCHMALZ.COM/10.01.06.03356