

Körüklü vantuz 2C (yuvarlak)

SDC2 30 PU 30/60 N042


Art.-Nr.: 10.01.06.03366



SDC2 30 PU 30/60 N042

Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	30.0 Shore A
Boyut	30.00
Körük Sayısı	2.5
Malzeme sertliği	60.0 Shore A



Tasarım verileri SDC2 30 PU 30/60 N042

Tasarım verileri

Attribute	Value
Yükseklik H2	4.50 mm
Yükseklik H	21.30 mm
Dış çap D1	25.5 mm
Kafa çapı Dk	16.5 mm
İç çap d1	7.2 mm
d2	14.4 mm
İç çap d	5.00 mm
Yay stroku Z	10.5 mm
Çap Ds	28.0 mm
Yükseklik H3	8.60 mm



WWW.SCHMALZ.COM/10.01.06.03366

Art.-Nr.: 10.01.06.03366



Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	30.0 Shore A
İş parçası yarıçapı dak (dışbükey)	12.5 mm
Çekme kuvveti	22.50 N
Emme kuvveti (-600mbar)	9.80 N
Boyut	30.00
Sıcaklık direnci	55.0 °C
Körük Sayısı	2.5
Malzeme sertliği	60.0 Shore A

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03366



WWW.SCHMALZ.COM/10.01.06.03366