


Art.-Nr.: 10.01.06.03367



SDC2 40 PU 30/60 N043

Technical data

Attribute	Value
Suction cup material	Polyurethane PU
Material hardness [Shore A]	30.0 Shore A
Size	40.00
Number of folds	2.5
Material hardness	60.0 Shore A



Design data SDC2 40 PU 30/60 N043

Design data

Attribute	Value
Height H2	6.00 mm
Height H	28.40 mm
Outside diameter D1	34.0 mm
Head diameter Dk	22.0 mm
Internal diameter d1	10.0 mm
d2	17.0 mm
Internal diameter d	6.50 mm
Spring stroke Z	14.0 mm
Diameter Ds	40.0 mm
Height H3	11.50 mm

Art.-Nr.: 10.01.06.03367

**Technical data**

Attribute	Value
Suction cup material	Polyurethane PU
Material hardness [Shore A]	30.0 Shore A
Workpiece radius min. (convex)	15.0 mm
Pull-off force	50.00 N
Suction force (-600mbar)	13.60 N
Size	40.00
Temperature resistance	55.0 °C
Number of folds	2.5
Material hardness	60.0 Shore A

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03367

