

Сильфонная присоска 2К (круглая)
SDC2 50 PU 30/60 N044




Art.-Nr.: 10.01.06.03368



SDC2 50 PU 30/60 N044

Технические данные

Attribute	Value
Материал присоски	Полиуретан PU
Твердость материала [Shore A]	30,0 Shore A
размер	50,00
Количество складок	2,5
Твердость материала	60,0 Shore A



Конструктивные данные SDC2 50 PU 30/60 N044

Конструктивные данные

Attribute	Value
Высота H2	8,00 mm
Высота H	35,50 mm
Наружный диаметр D1	42,5 mm
Диаметр головки Dk	27,5 mm
Внутренний диаметр d1	13,5 mm
d2	21,9 mm
Внутренний диаметр d	10,50 mm
Ход пружины Z	16,0 mm
Диаметр Ds	50,0 mm
Высота H3	14,40 mm



WWW.SCHMALZ.COM/10.01.06.03368

Сильфонная присоска 2К (круглая)
SDC2 50 PU 30/60 N044



Art.-Nr.: 10.01.06.03368



Технические данные

Attribute	Value
Материал присоски	Полиуретан PU
Твердость материала [Shore A]	30,0 Shore A
Радиус заготовки мин. (выпуклый)	20,0 mm
Сила отрыва	72,00 N
Всасывающая сила (-600 мбар)	22,60 N
размер	50,00
Термостойкость	55,0 °C
Количество складок	2,5
Твердость материала	60,0 Shore A

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03368



WWW.SCHMALZ.COM/10.01.06.03368