

SA-NIP N044 G3/8-AG DN800




Art.-Nr.: 10.01.06.03372



SA-NIP N044 G3/8-AG DN800

Технические данные

Attribute	Value
Семейство ниппелей	N 044
Материал	алюминий
Длина L1	25,00 mm
Номинальный диаметр dn	8,00 mm
Длина посадки	6,00 mm
Резьба G1	G3/8-AG



Конструктивные данные SA-NIP N044 G3/8-AG DN800

Конструктивные данные

Attribute	Value
Длина L1	25,00 mm
Длина L2	8,00 mm
Длина L	6,00 mm
Наружный диаметр D2	14,0 mm
Наружный диаметр D	15,00 mm
Номинальный диаметр dn	8,00 mm
Резьба G1	G3/8-AG
Длина резьбы LG1	10,0 mm
Размер гаечного ключа SW1	24,0 mm
Длина L3	1,00 mm



Технические данные

Attribute	Value
Семейство ниппелей	N 044
Материал	алюминий

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



WWW.SCHMALZ.COM/10.01.06.03372

Соединительный ниппель для вакуумной присоски

SA-NIP N044 G3/8-AG DN800



Art.-Nr.: 10.01.06.03372



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03372



WWW.SCHMALZ.COM/10.01.06.03372