




SAB 60 HT2-65 G1/4-IG

Çeşitli çaplarda mevcut olan vantuz SAB HT2, elastomer parçaya vulkanize edilmiş bağlantı nipelini ile birlikte teslim edilir.



Tasarım verileri SAB 60 HT2-65 G1/4-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65,0 Shore A
Boyut	60,00
Sıcaklık direnci	200,0 °C
Körük Sayısı	1,5
Bağlantı	G1/4-IG
Meme ucu malzemesi	Alüminyum

Tasarım verileri

Attribute	Value
Yükseklik H	46,30 mm
Dış çap D1	49,5 mm
Nominal çap dn	6,00 mm
Dış G1	G1/4"-F
Dış uzunluğu LG1	20,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	14,5 mm
Çap Ds	61,2 mm
Çap Dmax(S)	67,0 mm

Art.-Nr.: 10.01.06.03449

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65,0 Shore A
Hortum çapı (tavsiye edilen) d	6,0 mm
İş parçası yarıçapı dak (dışbükey)	30,0 mm
Çekme kuvveti	136,00 N
Emme kuvveti (-600mbar)	82,00 N
Ağırlık	65,1 g
Yanal kuvvet	126,0 N
Cilt	28,800 cm ³
Boyut	60,00
Körük Sayısı	1,5
Bağlantı	G1/4" -F
Ürün ailesi	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03449

WWW.SCHMALZ.COM/10.01.06.03449