




Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65,0 Shore A
Boyut	50,00
Sıcaklık direnci	200,0 °C
Körük Sayısı	1,5
Bağlantı	G1/4-AG
Meme ucu malzemesi	Alüminyum

SAB 50 HT2-65 G1/4-AG

Çeşitli çaplarda mevcut olan vantuz SAB HT2, elastomer parçaya vulkanize edilmiş bağlantı nipeli ile birlikte teslim edilir.



Tasarım verileri

Attribute	Value
Yükseklik H	36,90 mm
Dış çap D1	42,1 mm
Nominal çap dn	6,00 mm
Dış G1	G1/4"-M
Dış uzunluğu LG1	10,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	11,6 mm
Çap Ds	50,2 mm
Çap Dmax(S)	56,0 mm

Tasarım verileri SAB 50 HT2-65 G1/4-AG

Art.-Nr.: 10.01.06.03452



Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65,0 Shore A
Hortum çapı (tavsiye edilen) d	4,0 mm
İş parçası yarıçapı dak (dışbükey)	25,0 mm
Çekme kuvveti	91,00 N
Emme kuvveti (-600mbar)	53,00 N
Ağırlık	47,0 g
Yanal kuvvet	102,0 N
Cilt	16,100 cm ³
Boyut	50,00
Körük Sayısı	1,5
Bağlantı	G1/4"-M
Ürün ailesi	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03452

