


SPB2f 50 SI-55 SC090

Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	50.00
Number of folds	2.5
Material characteristics	FDA-compatible



Design data SPB2f 50 SI-55 SC090

Design data

Attribute	Value
Height H2	14.00 mm
Height H	45.60 mm
Outside diameter D1	41.6 mm
Head diameter Dk	31.0 mm
Internal diameter d1	24.8 mm
d2	21.0 mm
Internal diameter d	20.00 mm
Spring stroke Z	9.0 mm
Diameter Ds	49.7 mm
Height H3	16.00 mm

Art.-Nr.: 10.01.06.03560

**Technical data**

Attribute	Value
Nipple family	SC 090
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	12.0 mm
Suction force (-600mbar)	41.00 N
Weight	16.4 g
Volume	26.452 cm ³
Size	50.00
Number of folds	2.5
Suction force at -400 mbar	27.30 N
Suction force at -200 mbar	13.70 N
Product family	SPB2f

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03560

**Ordering Data Accessories 10.01.06.03560**

Typ		Item number
Schmalz-Connector	SC 090 NPT1/4-AG	10.01.06.03666
Schmalz-Connector	SC 090 NPT1/4-IG	10.01.06.03667
Schmalz-Connector	SC 090 NPT3/8-AG	10.01.06.03668
Schmalz-Connector	SC 090 NPT3/8-IG	10.01.06.03669
Sieve, round	SIEB 19.5x1 MS-A2 103	10.07.01.00321

