

Art.-Nr.: 10.01.06.03564



SPB4f 50 SI-HD-65 SC090


Technical data

Attribute	Value
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65.0 Shore A
Size	50.00
Number of folds	4.5

Suction cup SPB4f (elastomer part + connection element) with integrated bag stabilizer is delivered assembled. As an alternative the individual parts can also be ordered separately. To do this, the following ordering steps are required:

- Suction cup of type SPB4f (step 1) – elastomer part, available in various diameters
- Connection element of type SC (step 2) – available with various threads

Available accessories: filter screen, hose clamp



Design data SPB4f 50 SI-HD-65 SC090

Design data

Attribute	Value
Height H2	14.00 mm
Height H	65.00 mm
Outside diameter D1	41.6 mm
Head diameter Dk	31.0 mm
Internal diameter d1	24.8 mm
d2	21.0 mm
Internal diameter d	20.00 mm
Spring stroke Z	26.0 mm
Diameter Ds	49.7 mm
Height H3	16.00 mm
Diameter Dmax(S)	52.0 mm

Art.-Nr.: 10.01.06.03564

**Technical data**

Attribute	Value
Nipple family	SC 090
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65.0 Shore A
Suction force (-600mbar)	41.00 N
Weight	22.60 g
Volume	33.110 cm ³
Size	50.00
Number of folds	4.5
Suction force at -400 mbar	27.30 N
Suction force at -200 mbar	13.70 N
Product family	SPB4f

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03564

