

Art.-Nr.: 10.01.06.03632



SAB 80 HT1-60 G1/2-IG


Suction cup SAB HT1, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	80.00
Number of folds	1.5
Connection	G1/2-IG
Nipple material	Aluminum

Design data

Attribute	Value
Height H	49.90 mm
Outside diameter D1	63.6 mm
Nominal diameter dn	6.00 mm
Thread G1	G1/2"-F
Thread length LG1	15.0 mm
Key width SW1	24.0 mm
Spring stroke Z	22.1 mm
Diameter Ds	81.1 mm
Diameter Dmax(S)	89.0 mm



Design data SAB 80 HT1-60 G1/2-IG



Art.-Nr.: 10.01.06.03632

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	75.0 mm
Pull-off force	221.00 N
Suction force (-600mbar)	135.00 N
Weight	57.8 g
Lateral force	145.0 N
Lateral force oily surface	140.0 N
Volume	67.600 cm ³
Size	80.00
Number of folds	1.5
Product family	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03632

