




SAB 100 HT1-60 G1/2-IG

Çeşitli çaplarda mevcut olan vantuz SAB HT1, elastomer parçaya vulkanize edilmiş bağlantı nipelini ile birlikte teslim edilir.



Tasarım verileri SAB 100 HT1-60 G1/2-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	100,00
Körük Sayısı	1,5
Bağlantı	G1/2-IG
Meme ucu malzemesi	Alüminyum

Tasarım verileri

Attribute	Value
Yükseklik H	56,60 mm
Dış çap D1	77,0 mm
Nominal çap dn	6,00 mm
Dış G1	G1/2"-F
Dış uzunluğu LG1	15,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	25,8 mm
Çap Ds	100,8 mm
Çap Dmax(S)	110,0 mm

Art.-Nr.: 10.01.06.03679

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Hortum çapı (tavsiye edilen) d	6,0 mm
İş parçası yarıçapı dak (dışbükey)	90,0 mm
Çekme kuvveti	357,00 N
Emme kuvveti (-600mbar)	190,00 N
Ağırlık	88,20 g
Yanal kuvvet	220,0 N
Yanal kuvvet yağlı yüzey	214,0 N
Cilt	115,000 cm ³
Boyut	100,00
Körük Sayısı	1,5
Ürün ailesi	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03679

WWW.SCHMALZ.COM/10.01.06.03679