




FG 3 SI-CO-55 N055

Технические данные

Attribute	Value
Материал присоски	Силикон SI проводящий
Твердость материала [Shore A]	55,0 Shore A
размер	3,00
Количество складок	2,5



Конструктивные данные FG 3 SI-CO-55 N055

Конструктивные данные

Attribute	Value
Высота H2	2,10 mm
Высота H	6,70 mm
Наружный диаметр D1	3,6 mm
Диаметр головки Dk	3,6 mm
Внутренний диаметр d1	2,3 mm
d2	1,8 mm
Внутренний диаметр d	1,70 mm
Ход пружины Z	1,1 mm
Диаметр Ds	3,0 mm
Высота H3	2,70 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Art.-Nr.: 10.01.06.03707



Технические данные

Attribute	Value
Семейство ниппелей	N 055
Материал присоски	Силикон SI проводящий
Твердость материала [Shore A]	55,0 Shore A
Внутренний диаметр шланга (реком.) d	2,0 mm
Радиус заготовки мин. (выпуклый)	4,0 mm
Сила отрыва	0,40 N
Всасывающая сила (-600 мбар)	0,15 N
Объем	0,022 cm ³
размер	3,00
Количество складок	2,5
Семейство продуктов	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03707



WWW.SCHMALZ.COM/10.01.06.03707