

Bellows suction cup 2C (round)

SDC1 20 PU 30/60 N042

Art.-Nr.: 10.01.06.04048




SDC1 20 PU 30/60 N042

Technical data

Attribute	Value
Suction cup material	Polyurethane PU
Material hardness [Shore A]	30.0 Shore A
Size	20.00
Number of folds	1.5
Material hardness	60.0 Shore A

Design data

Attribute	Value
Height H2	4.50 mm
Height H	18.00 mm
Outside diameter D1	22.0 mm
Head diameter Dk	12.0 mm
Internal diameter d1	7.5 mm
d2	10.0 mm
Internal diameter d	5.00 mm
Spring stroke Z	7.5 mm
Diameter Ds	20.0 mm
Height H3	7.00 mm



Design data SDC1 20 PU 30/60 N042



WWW.SCHMALZ.COM/10.01.06.04048

Art.-Nr.: 10.01.06.04048

**Technical data**

Attribute	Value
Suction cup material	Polyurethane PU
Material hardness [Shore A]	30.0 Shore A
Workpiece radius min. (convex)	10.0 mm
Pull-off force	12.60 N
Suction force (-600mbar)	4.70 N
Volume	4.000 cm ³
Size	20.00
Temperature resistance	55.0 °C
Number of folds	1.5
Material hardness	60.0 Shore A

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04048

