

Сильфонная присоска 2К (круглая)
SDC1 20 PU 30/60 N042




Art.-Nr.: 10.01.06.04048



SDC1 20 PU 30/60 N042

Технические данные

Attribute	Value
Материал присоски	Полиуретан PU
Твердость материала [Shore A]	30,0 Shore A
размер	20,00
Количество складок	1,5
Твердость материала	60,0 Shore A



Конструктивные данные SDC1 20 PU 30/60 N042

Конструктивные данные

Attribute	Value
Высота H2	4,50 mm
Высота H	18,00 mm
Наружный диаметр D1	22,0 mm
Диаметр головки Dk	12,0 mm
Внутренний диаметр d1	7,5 mm
d2	10,0 mm
Внутренний диаметр d	5,00 mm
Ход пружины Z	7,5 mm
Диаметр Ds	20,0 mm
Высота H3	7,00 mm



WWW.SCHMALZ.COM/10.01.06.04048

Сильфонная присоска 2К (круглая)
SDC1 20 PU 30/60 N042



Art.-Nr.: 10.01.06.04048



Технические данные

Attribute	Value
Материал присоски	Полиуретан PU
Твердость материала [Shore A]	30,0 Shore A
Радиус заготовки мин. (выпуклый)	10,0 mm
Сила отрыва	12,60 N
Всасывающая сила (-600 мбар)	4,70 N
Объем	4,000 cm ³
размер	20,00
Термостойкость	55,0 °C
Количество складок	1,5
Твердость материала	60,0 Shore A

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04048



WWW.SCHMALZ.COM/10.01.06.04048