

Bellows suction cup 2C (round)

SDC1 40 PU 30/60 N043



Art.-Nr.: 10.01.06.04050




SDC1 40 PU 30/60 N043

Technical data

Attribute	Value
Suction cup material	Polyurethane PU
Material hardness [Shore A]	30.0 Shore A
Size	40.00
Number of folds	1.5
Material hardness	60.0 Shore A

Design data

Attribute	Value
Height H2	6.00 mm
Height H	22.40 mm
Outside diameter D1	42.4 mm
Head diameter Dk	22.4 mm
Internal diameter d1	12.8 mm
d2	24.0 mm
Internal diameter d	6.50 mm
Spring stroke Z	9.5 mm
Diameter Ds	40.0 mm
Height H3	12.40 mm



Design data SDC1 40 PU 30/60 N043



WWW.SCHMALZ.COM/10.01.06.04050

Art.-Nr.: 10.01.06.04050

**Technical data**

Attribute	Value
Suction cup material	Polyurethane PU
Material hardness [Shore A]	30.0 Shore A
Workpiece radius min. (convex)	20.0 mm
Pull-off force	57.50 N
Suction force (-600mbar)	27.10 N
Volume	9.800 cm ³
Size	40.00
Temperature resistance	55.0 °C
Number of folds	1.5
Material hardness	60.0 Shore A

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04050

