

Сильфонная присоска 2К (круглая)
SDC1 40 PU 30/60 N043




Art.-Nr.: 10.01.06.04050



SDC1 40 PU 30/60 N043

Технические данные

Attribute	Value
Материал присоски	Полиуретан PU
Твердость материала [Shore A]	30,0 Shore A
размер	40,00
Количество складок	1,5
Твердость материала	60,0 Shore A



Конструктивные данные SDC1 40 PU 30/60 N043

Конструктивные данные

Attribute	Value
Высота H2	6,00 mm
Высота H	22,40 mm
Наружный диаметр D1	42,4 mm
Диаметр головки Dk	22,4 mm
Внутренний диаметр d1	12,8 mm
d2	24,0 mm
Внутренний диаметр d	6,50 mm
Ход пружины Z	9,5 mm
Диаметр Ds	40,0 mm
Высота H3	12,40 mm



WWW.SCHMALZ.COM/10.01.06.04050

Сильфонная присоска 2К (круглая)
SDC1 40 PU 30/60 N043



Art.-Nr.: 10.01.06.04050



Технические данные

Attribute	Value
Материал присоски	Полиуретан PU
Твердость материала [Shore A]	30,0 Shore A
Радиус заготовки мин. (выпуклый)	20,0 mm
Сила отрыва	57,50 N
Всасывающая сила (-600 мбар)	27,10 N
Объем	9,800 cm ³
размер	40,00
Термостойкость	55,0 °C
Количество складок	1,5
Твердость материала	60,0 Shore A

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04050



WWW.SCHMALZ.COM/10.01.06.04050