

Сильфонная присоска 2К (круглая)
SDC1 50 PU 30/60 N044




Art.-Nr.: 10.01.06.04051



SDC1 50 PU 30/60 N044

Технические данные

Attribute	Value
Материал присоски	Полиуретан PU
Твердость материала [Shore A]	30,0 Shore A
размер	50,00
Количество складок	1,5
Твердость материала	60,0 Shore A



Конструктивные данные SDC1 50 PU 30/60 N044

Конструктивные данные

Attribute	Value
Высота H2	8,00 mm
Высота H	29,20 mm
Наружный диаметр D1	52,5 mm
Диаметр головки Dk	28,0 mm
Внутренний диаметр d1	14,0 mm
d2	30,0 mm
Внутренний диаметр d	10,50 mm
Ход пружины Z	13,5 mm
Диаметр Ds	50,0 mm
Высота H3	15,00 mm



WWW.SCHMALZ.COM/10.01.06.04051

Сильфонная присоска 2К (круглая)
SDC1 50 PU 30/60 N044



Art.-Nr.: 10.01.06.04051



Технические данные

Attribute	Value
Материал присоски	Полиуретан PU
Твердость материала [Shore A]	30,0 Shore A
Радиус заготовки мин. (выпуклый)	25,0 mm
Сила отрыва	93,30 N
Всасывающая сила (-600 мбар)	42,40 N
Объем	21,400 cm ³
размер	50,00
Термостойкость	55,0 °C
Количество складок	1,5
Твердость материала	60,0 Shore A

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04051



WWW.SCHMALZ.COM/10.01.06.04051