

Körüklü vantuz 2C (yuvarlak)

SDC1 50 PU 30/60 N044


Art.-Nr.: 10.01.06.04051



SDC1 50 PU 30/60 N044

Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	30.0 Shore A
Boyut	50.00
Körük Sayısı	1.5
Malzeme sertliği	60.0 Shore A



Tasarım verileri SDC1 50 PU 30/60 N044

Tasarım verileri

Attribute	Value
Yükseklik H2	8.00 mm
Yükseklik H	29.20 mm
Dış çap D1	52.5 mm
Kafa çapı Dk	28.0 mm
İç çap d1	14.0 mm
d2	30.0 mm
İç çap d	10.50 mm
Yay stroku Z	13.5 mm
Çap Ds	50.0 mm
Yükseklik H3	15.00 mm



WWW.SCHMALZ.COM/10.01.06.04051

Art.-Nr.: 10.01.06.04051



Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	30.0 Shore A
İş parçası yarıçapı dak (dışbükey)	25.0 mm
Çekme kuvveti	93.30 N
Emme kuvveti (-600mbar)	42.40 N
Cilt	21.400 cm ³
Boyut	50.00
Sıcaklık direnci	55.0 °C
Körük Sayısı	1.5
Malzeme sertliği	60.0 Shore A

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04051



WWW.SCHMALZ.COM/10.01.06.04051