


Сильфонная присоска (круглая)
SPB2f 15 SI-55 SC040




Art.-Nr.: 10.01.06.04090



SPB2f 15 SI-55 SC040

Технические данные

Attribute	Value
Материал присоски	Силикон SI
Твердость материала [Shore A]	55,0 Shore A
размер	15,00
Количество складок	2,5
Характеристики материала	Совместимый с FDA



Конструктивные данные SPB2f 15 SI-55 SC040

Конструктивные данные

Attribute	Value
Высота H2	4,60 mm
Высота H	20,30 mm
Наружный диаметр D1	14,0 mm
Диаметр головки Dk	13,1 mm
Внутренний диаметр d1	10,5 mm
d2	4,0 mm
Внутренний диаметр d	7,50 mm
Ход пружины Z	7,3 mm
Диаметр Ds	15,0 mm
Высота H3	6,60 mm



WWW.SCHMALZ.COM/10.01.06.04090

Сильфонная присоска (круглая)
SPB2f 15 SI-55 SC040



Art.-Nr.: 10.01.06.04090



Технические данные

Attribute	Value
Семейство ниппелей	SC 040
Материал присоски	Силикон SI
Твердость материала [Shore A]	55,0 Shore A
Всасывающая сила (-600 мбар)	0,75 N
Вес	1,5 g
Объем	1,200 cm ³
размер	15,00
Количество складок	2,5
Всасывающая сила при -400 мбар	0,50 N
Всасывающая сила при -200 мбар	0,25 N
Семейство продуктов	SPB2f

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04090



WWW.SCHMALZ.COM/10.01.06.04090