

Сильфонная присоска (круглая)
FGA 4 SI-CO-55 N003




Art.-Nr.: 10.01.06.04094



FGA 4 SI-CO-55 N003

Технические данные

Attribute	Value
Материал присоски	Силикон SI проводящий
Твердость материала [Shore A]	55,0 Shore A
размер	4,00
Количество складок	1,5



Конструктивные данные FGA 4 SI-CO-55 N003

Конструктивные данные

Attribute	Value
Высота H2	1,50 mm
Высота H	5,50 mm
Наружный диаметр D1	4,6 mm
Диаметр головки Dk	4,0 mm
Внутренний диаметр d1	3,0 mm
d2	2,5 mm
Внутренний диаметр d	2,00 mm
Ход пружины Z	1,5 mm
Диаметр Ds	4,0 mm
Высота H3	2,60 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3



WWW.SCHMALZ.COM/10.01.06.04094

Сильфонная присоска (круглая)
FGA 4 SI-CO-55 N003



Art.-Nr.: 10.01.06.04094



Технические данные

Attribute	Value
Материал присоски	Силикон SI проводящий
Радиус заготовки мин. (выпуклый)	1,5 mm
Всасывающая сила (-600 мбар)	0,29 N
Вес	0,1 g
размер	4,00
Количество складок	1,5
Семейство продуктов	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04094



WWW.SCHMALZ.COM/10.01.06.04094