

Art.-Nr.: 10.01.06.04149



FG 20 SI-HD-65 N016


Technical data

Attribute	Value
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65.0 Shore A
Size	20.00

Design data

Attribute	Value
Height H2	3.80 mm
Height H	22.10 mm
Outside diameter D1	20.0 mm
Head diameter Dk	10.0 mm
d2	10.5 mm
Internal diameter d	4.50 mm
Spring stroke Z	9.0 mm
Diameter Ds	20.0 mm
Height H3	9.00 mm
Diameter Dmax(S)	21.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



Design data FG 20 SI-HD-65 N016

Bellows suction cup SI-HD (round)
FG 20 SI-HD-65 N016



Art.-Nr.: 10.01.06.04149



Technical data

Attribute	Value
Nipple family	N 016
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65.0 Shore A
Workpiece radius min. (convex)	30.0 mm
Size	20.00
Number of folds	2.5

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04149



Ordering Data Accessories 10.01.06.04149

Typ		Item number
Suction cup connection nipple	SA-NIP N016 G1/8-AG DN310	10.01.06.04062
Suction cup connection nipple	SA-NIP N016 M5-AG DN250	10.01.06.04365
Suction cup connection nipple	SA-NIP N016 M5-IG DN310	10.01.06.04689
Suction cup connection nipple	SA-NIP N016 G1/8-IG DN310	10.01.06.04690



WWW.SCHMALZ.COM/10.01.06.04149