


Bellows suction cup SI-HD (round)
FGA 20 SI-HD-65 N016




Art.-Nr.: 10.01.06.04150



Technical data

Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65.0 Shore A
Size	20.00
Number of folds	1.5
Material characteristics	FDA-compatible

FGA 20 SI-HD-65 N016



Design data

Height H2	3.80 mm
Height H	15.20 mm
Outside diameter D1	19.9 mm
Head diameter Dk	10.0 mm
d2	11.0 mm
Internal diameter d	4.50 mm
Spring stroke Z	4.4 mm
Diameter Ds	18.1 mm
Height H3	8.70 mm
Diameter Dmax(S)	21.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FGA 20 SI-HD-65 N016



WWW.SCHMALZ.COM/10.01.06.04150

Bellows suction cup SI-HD (round)
FGA 20 SI-HD-65 N016



Art.-Nr.: 10.01.06.04150



Technical data

Suction cup material	Silicone SI-HD
Workpiece radius min. (convex)	8.5 mm
Suction force (-600mbar)	4.70 N
Weight	1.70 g
Size	20.00
Number of folds	1.5
Product family	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Ordering Data Accessories 10.01.06.04150

Typ		Item number
Suction cup connection nipple	SA-NIP N016 G1/8-IG DN350	10.01.06.05731
Suction cup connection nipple	SA-NIP N016 G1/8-AG DN350	10.01.06.05735
Suction cup connection nipple	SA-NIP N016 M5-AG DN250	10.01.06.00123
Suction cup connection nipple	SA-NIP N016 G1/8-AG DN310	10.01.06.04062
Suction cup connection nipple	SA-NIP N016 M5-AG DN250	10.01.06.04365
Suction cup connection nipple	SA-NIP N016 M5-IG DN310	10.01.06.04689
Suction cup connection nipple	SA-NIP N016 G1/8-IG DN310	10.01.06.04690



WWW.SCHMALZ.COM/10.01.06.04150