

Bellows suction cup (round)

FGA 20 NBR-ESD-55 N062




Art.-Nr.: 10.01.06.04258



Technical data

Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Size	20.00
Number of folds	1.5

FGA 20 NBR-ESD-55 N062



Design data

Height H2	3.80 mm
Height H	15.20 mm
Outside diameter D1	19.9 mm
Head diameter Dk	10.0 mm
d2	11.0 mm
Internal diameter d	4.50 mm
Spring stroke Z	4.4 mm
Diameter Ds	18.1 mm
Height H3	8.70 mm
Diameter Dmax(S)	21.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FGA 20 NBR-ESD-55 N062



WWW.SCHMALZ.COM/10.01.06.04258

Art.-Nr.: 10.01.06.04258

**Technical data**

Suction cup material	Nitrile rubber NBR-ESD
Workpiece radius min. (convex)	8.5 mm
Suction force (-600mbar)	4.70 N
Weight	1.70 g
Size	20.00
Number of folds	1.5
Product family	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Accessories 10.01.06.04258**

Typ		Item number
Suction cup connection nipple	SA-NIP N062 M5-AG DN250	10.01.06.05668
Suction cup connection nipple	SA-NIP N062 G1/8-IG DN350	10.01.06.05669
Suction cup connection nipple	SA-NIP N062 G1/8-AG DN350	10.01.06.05670

