

Bellows suction cup (round)

FG 5 NBR-ESD-55 N017




Art.-Nr.: 10.01.06.04215



Technical data

Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Size	5.00
Number of folds	2.5

FG 5 NBR-ESD-55 N017



Design data

Height H2	8.00 mm
Height H	14.00 mm
Outside diameter D1	6.0 mm
Head diameter Dk	7.0 mm
d2	2.6 mm
Internal diameter d	3.50 mm
Spring stroke Z	2.0 mm
Diameter Ds	5.0 mm
Diameter Dmax(S)	6.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FG 5 NBR-ESD-55 N017



WWW.SCHMALZ.COM/10.01.06.04215

Art.-Nr.: 10.01.06.04215

**Technical data**

Nipple family	N 017
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	2.0 mm
Pull-off force	0.80 N
Suction force (-600mbar)	0.32 N
Weight	0.40 g
Volume	0.137 cm ³
Size	5.00
Number of folds	2.5
Product family	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Accessories 10.01.06.04215**

Typ		Item number
Suction cup connection nipple	SA-NIP N017 M5-AG DN200	10.01.06.00314
Suction cup connection nipple	SA-NIP N017 M5-IG DN200	10.01.06.00313

