

Art.-Nr.: 10.01.06.04318

**Technical data**


Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Size	6.00
Number of folds	1.5
Connection	M5-F
Vacuum connection	M5-F
Nipple material	Aluminum

FSGA 6 NBR-ESD-55 M5-IG

Suction cup FSGA (elastomer part + connection nipple) is delivered unassembled (diameters of 33 mm and more are assembled). The delivery consists of:

- Suction cup of type FGA – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup FGA, connection nipple SA-NIP

**Design data**

Height H	19.00 mm
Nominal diameter dn	2.00 mm
d2	3.0 mm
Thread G1	M5-F
Thread length LG1	5.5 mm
Key width SW1	8.0 mm
Spring stroke Z	2.0 mm
Diameter Ds	5.7 mm
Diameter Dmax(S)	8.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FSGA 6 NBR-ESD-55 M5-IG



Art.-Nr.: 10.01.06.04318

**Technical data**

Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	4.0 mm
Pull-off force	1.40 N
Suction force (-600mbar)	0.40 N
Weight	1.50 g
Volume	1.511 cm ³
Size	6.00
Number of folds	1.5
Product family	FSGA
Connection	M5-IG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Spare Parts 10.01.06.04318**

Typ		Item number
Suction cup connection nipple	SA-NIP N004 M5-IG DN200	10.01.01.03518
Bellows suction cup (round)	FGA 6 NBR-ESD-55 N004	10.01.06.04135

