

Art.-Nr.: 10.01.06.04333

**Technical data**


Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Size	5.00
Number of folds	2.5
Connection	M5-F
Vacuum connection	M5-F
Nipple material	Aluminum

FSG 5 NBR-ESD-55 M5-IG

Suction cup FSG (elastomer part + connection nipple) is delivered unassembled (assembled from a diameter of 32 mm). The delivery consists of:

- Suction cup of type FG – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup FG, connection nipple SA-NIP

**Design data**

Height H	24.00 mm
Nominal diameter dn	2.00 mm
d2	2.6 mm
Thread G1	M5-F
Thread length LG1	5.5 mm
Key width SW1	8.0 mm
Spring stroke Z	2.0 mm
Diameter Ds	5.0 mm
Diameter Dmax(S)	7.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FSG 5 NBR-ESD-55 M5-IG



Art.-Nr.: 10.01.06.04333

**Technical data**

Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	2.0 mm
Workpiece radius min. (convex)	7.5 mm
Pull-off force	0.80 N
Suction force (-600mbar)	0.32 N
Weight	1.70 g
Volume	0.033 cm ³
Size	5.00
Number of folds	2.5
Product family	FSG
Connection	M5-IG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Spare Parts 10.01.06.04333**

Typ		Item number
Bellows suction cup (round)	FG 5 NBR-ESD-55 N017	10.01.06.04215
Suction cup connection nipple	SA-NIP N017 M5-IG DN200	10.01.06.00313

