


Art.-Nr.: 10.01.06.04382




SFB1 25 HT1-60 SC040

**Technical data**

| Attribute                   | Value                         |
|-----------------------------|-------------------------------|
| Suction cup material        | High temperature material HT1 |
| Material hardness [Shore A] | 60.0 Shore A                  |
| Size                        | 25.00                         |
| Number of folds             | 1.5                           |

**Design data**

| Attribute            | Value    |
|----------------------|----------|
| Height H2            | 4.70 mm  |
| Height H             | 19.20 mm |
| Outside diameter D1  | 18.8 mm  |
| Head diameter Dk     | 13.0 mm  |
| Internal diameter d1 | 10.4 mm  |
| d2                   | 8.2 mm   |
| Internal diameter d  | 7.50 mm  |
| Spring stroke Z      | 6.5 mm   |
| Diameter Ds          | 25.0 mm  |
| Diameter Dmax(S)     | 26.5 mm  |



Design data SFB1 25 HT1-60 SC040

Art.-Nr.: 10.01.06.04382

**Technical data**

| Attribute                      | Value                         |
|--------------------------------|-------------------------------|
| Nipple family                  | SC 040                        |
| Suction cup material           | High temperature material HT1 |
| Material hardness [Shore A]    | 60.0 Shore A                  |
| Workpiece radius min. (convex) | 18.0 mm                       |
| Pull-off force                 | 18.50 N                       |
| Suction force (-600mbar)       | 3.20 N                        |
| Volume                         | 1.880 cm <sup>3</sup>         |
| Size                           | 25.00                         |
| Number of folds                | 1.5                           |
| Product family                 | SFB1                          |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.06.04382](http://www.schmalz.com/10.01.06.04382)

**Ordering Data Accessories 10.01.06.04382**

| Typ               |                | Item number    |
|-------------------|----------------|----------------|
| Schmalz-Connector | SC 040 G1/8-AG | 10.01.06.02490 |
| Schmalz-Connector | SC 040 G1/8-IG | 10.01.06.02482 |

**Ordering Data Spare Parts 10.01.06.04382**

| Typ               |              | Item number    |
|-------------------|--------------|----------------|
| Schmalz-Connector | SC 040 M5-AG | 10.01.06.04346 |

