




SFB1 15 HT1-60 G1/8-AG

Vantuz SFF / SFB1 (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF / SFB1, bağlantı nipeli SC



Tasarım verileri SFB1 15 HT1-60 G1/8-AG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Boyut	15.00

Tasarım verileri

Attribute	Value
Yükseklik H	22.00 mm
Nominal çap dn	4.10 mm
d2	4.7 mm
Diş uzunluğu LG1	7.5 mm
Anahtar boyutu SW1	14.0 mm
Yay stroku Z	4.0 mm
Çap Ds	15.0 mm
Çap Dmax(S)	16.0 mm
Diş G1	G1/8-AG

Art.-Nr.: 10.01.06.04399

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Çekme kuvveti	6.10 N
Emme kuvveti (-600mbar)	1.00 N
Cilt	0.800 cm ³
Boyut	15.00
Körük Sayısı	1.5
Ürün ailesi	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04399

**Yedek parçalar için sipariş verileri 10.01.06.04399**

Typ	Ürün numarası
Körüklü vantuz (yuvarlak)	SFB1 15 HT1-60 SC040 10.01.06.04380
Schmalz-Konnektör	SC 040 G1/8-AG 10.01.06.02490

