

Bellows suction cup (round)

FGB 12 SI-55 N016

Art.-Nr.: 10.01.06.04502



FGB 12 SI-55 N016

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliđi [Shore A]	55.0 Shore A
Boyut	12.00
Körük Sayısı	3.5

Tasarım verileri

Attribute	Value
Yükseklik H2	6.50 mm
Yükseklik H	24.50 mm
Dış çap D1	12.0 mm
Kafa çapı Dk	10.0 mm
d2	5.0 mm
İç çap d	4.50 mm
Yay stroku Z	11.0 mm
Çap Ds	11.9 mm
Çap Dmax(S)	13.0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri FGB 12 SI-55 N016



WWW.SCHMALZ.COM/10.01.06.04502

Art.-Nr.: 10.01.06.04502



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Emme kuvveti (-600mbar)	1.18 N
Ağırlık	1.3 g
Cilt	0.958 cm ³
Boyut	12.00
Körük Sayısı	3.5
Ürün ailesi	FGB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04502



WWW.SCHMALZ.COM/10.01.06.04502